



Sample photo

**Order symbol:** ALN 122208  
**Product nbr:** 7811230  
**Description:** Enclosure  
**Remarks:** Aluminium

**EAN:** 6418074016119  
**EI. number:**  
 Finland: 3420049  
 Electric No. 8212045693  
 Denmark:  
 Electric No. Sweden: 2536321

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

| Dimensions:                         |                 |        |     | Accessories:                                  |                              |
|-------------------------------------|-----------------|--------|-----|---|------------------------------|
| Length                              | Width           | Height |     |   |                              |
| mm:                                 | 222             | 125    | 81  | ARH 22  | DIN-35 Mounting rail         |
| inch:                               | 8.7             | 4.9    | 3.2 | MR 75005                                      | Selftapping taptite screw M5 |
| <b>Materials:</b>                   |                 |        |     | MRS 28541                                     | Wall fastening lug (2 pcs)   |
| <b>Material:</b>                    | Aluminium       |        |     | PH A & AH A/B                                 | Hinge set                    |
| <b>Base colour:</b>                 | RAL 7001        |        |     | <b>Rating:</b>                                |                              |
| <b>Cover screws material:</b>       | Stainless steel |        |     | Ingress Protection (EN 60529): IP66/IP67/IP68 |                              |
| <b>Cover colour:</b>                | RAL 7001        |        |     | Impact Resistance (EN 62262): IK08            |                              |
| <b>Gasket material:</b>             | Polyurethane    |        |     | NEMA Class: NEMA 1, 4, 4X, 12, 13             |                              |
| <b>Temperatures:</b>                |                 |        |     | <b>Certificates:</b>                          |                              |
| <b>Temperature °C (short term):</b> | -50 ... 140 °C  |        |     | Underwriters Laboratories                     |                              |
| <b>Temperature °C (continuous):</b> | -50 ... 80 °C   |        |     | SGS Fimko                                     |                              |
| <b>Temperature °F (short term):</b> | -60 ... 285 °F  |        |     |   |                              |
| <b>Temperature °F (continuous):</b> | -60 ... 175 °F  |        |     |   |                              |
| <b>Accessories:</b>                 |                 |        |     |   |                              |
| AM 1222                             | Mounting plate  |        |     |   |                              |

