



Sample photo

Order symbol: ALN 316018
Product nbr: 7811480
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016263
EI. number:
 Finland: 3420008
 Electric No. 8212045868
 Denmark:
 Electric No. Sweden: 7811480

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	600	310	180	ARH 60	DIN-35 Mounting rail
inch:	23.6	12.2	7.1	MRS 28541	Wall fastening lug (2 pcs)
				PH A & AH A/B	Hinge set

Materials:		Rating:
Material:	Aluminium	Ingress Protection (EN 60529): IP66/IP67/IP68
Base colour:	RAL 7001	Impact Resistance (EN 62262): IK08
Cover screws material:	Stainless steel	NEMA Class: NEMA 1, 4, 4X, 12, 13
Cover colour:	RAL 7001	

Temperatures:	
Temperature °C (short term):	-50 ... 140 °C
Temperature °C (continuous):	-50 ... 80 °C
Temperature °F (short term):	-60 ... 285 °F
Temperature °F (continuous):	-60 ... 175 °F

Accessories:	
AM 3160	Mounting plate

