

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300960034](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: Liquid-Tight Grip Strain Relief, 1/2" NPT, Straight Male, Mesh Length 0.098m (3.875")

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159
 UL E61303

General

Product Family Cable Grips
 Series [130096](#)
 Eye Type N/A
 NEMA Rating NEMA 4
 O-Ring N/A
 Overview [Strain-Relief Cord Grips](#)
 Product Literature Order No 987651-6081
 Product Name Liquid-Tight
 Type Strain Relief Grip
 UPC 78678836370
 Use With 1/2" NPT MAX-LOC Lock Nut [130099-0143](#) , MAX-LOC O-Ring, 1/2" NPT [130180-0314](#) , 1/2" NPT MAX-LOC Gasket [130099-0149](#)
 Woodhead Yes

Physical

Approximate Break Strength N/A
 Bale Length N/A
 Body Style Straight
 Cable Diameter N/A
 Color - Grommet N/A
 Gender Male
 Material - Body Malleable Iron, Zinc Plated Steel
 Material - Grip Stainless Steel
 Mesh Length 0.098m (3.875")
 Number of Holes N/A
 Thread Size 1/2" NPT

Material Info

Engineering Number 36370

Reference - Drawing Numbers

Sales Drawing SD-130096-100



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed
 ELV Not Reviewed
 RoHS Phthalates Not Reviewed

Search Parts in this Series

[130096 Series](#)