

PRODUCT INTRODUCTION

MODEL 29-9505

CATEGORY: PORTABLE JUMPSTARTER



MULTI SAFETY PROTECTION 2.0

20000mAh 3.7V
LiPOLYMER BATTERY(88Wh)

1000A PEAK CURRENT
180w DC POWER
8.0L DIESEL(I12)
3.1A USB OUTPUT

Battery Smart clamps T104
Patent No. ZL201320403362.6



Name	Portable JumpStarter
Version	Max Version
Capacity	74Wh/20000mAh,3.7V
Weight	640g
Fully Charged Time	DC15V/1A: about 6-7 hours
Design	Xtreme Power Design
Dimensions(L*W*H)	182x85x45mm
Built-in Battery	High Rate Discharge Lithium Polymer Batteries
Input Recharging	Adapter:DC15V/1A
Charge mode	CC/CV
ECS Output	Support 12V Battery System Vehicle
Output	USB: 5V/1A; 5V/2.1A DC: 12-18V/15A(Max)
Bulb Type	Ultra bright LED light/SOS/Blink
Peak amps	1000A
Operation Temperature	-20 C~60 C
Operation Humidity	10%~90%
Lifecycle	>500 times
Safety Technology	MultiSafety Protection V2.0
Package include	1 x Car jump starter 1 x Car Charger 1 x Power Adapter 1 x user manual 1 x Battery Smart clamps T104 1 x Cigarette Lighter 1 x USB charging cable
Color	Green Black

