

L-1025903

L-1

L-1 LED T100 AG 700 930 CLA GB

EAN-nr: 7040670259035

Stock code: C



L-1 is a traditional task light with parallel, spring-balanced, three-pivot arm made of steel, with aluminium shade. A LED version is now available.



Light source	
Number of lamps	1
Lamp power (W)	7
Light source	LED
Lumen value supplied light source (lm)	350
Lumen/Watt	59
Colour rendering and colour temperature	CRI > 90, 3000K
Luminous flux decline (LLMF) 50000h Ta25	0.70
MacAdam step	3
Median useful life (IEC 62717) Ta25	50000h L70B50
Lumen Out	711
Technical data	
Maximum ambient temperature (°C)	25
IP classification	20
Optic	
Optic	SYM = Symmetric
Lightdistribution Up/Down	0/100

Electrical data	
Maximum voltage (V)	240
Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Voltage from (V)	100
Total consumption (W)	12
Dimensions	
Net weight (kg)	1,9
Arm length (cm)	100
Body	
Body material	Steel
Colour of body	Aluminium-grey
Ballast	
Type of Ballast	AC/DC = alternating current/ direct current
Wiring Accessories	Timer

L-1025903

L-1

Drawings

