



Search



Rollover image to zoom



DCF887D2 20V MAX* XR 1/4" 3-SPEED IMPACT DRIVER KIT (2.0AH)

★★★★★ 5.0 (1) [WRITE A REVIEW](#)

The DCF887D2 20V MAX* XR Brushless 1/4" 3-Speed Impact Driver is compact for fitting in tight spaces and increasing productivity. Three LED lights make it ideal for working in the dark.

BUY NOW

SHARE THIS PRODUCT:

IMPORTANT LINKS

FEATURES & SPECS

WARRANTY

USER REVIEWS

FEATURES & SPECS

FEATURES

- DEWALT built brushless motor and XR Lith-Ion batteries deliver more run time and capacity over standard units
- 3-speed settings for optimized application versatility
- Precision drive in speed 1 for precision applications and added control
- 3 LEDs with 20-second delay after trigger release, provide visibility without shadows
- One-handed loading 1/4" hex chuck with easy grip sleeve, accepts 1" bit tips

- Compact and lightweight design to fit into tight areas (6 mm shorter than the previous DCF886)

SPECIFICATIONS

ANVIL TYPE	1/4" HEX
CHUCK TYPE	QUICK RELEASE
IMPACTS/MIN	3600 IPM
MAX TORQUE (IN-LBS)	1825 IN-LBS
NO LOAD SPEED	0-1,000/ 2,800/ 3,250
POWER TOOL TYPE	CORDLESS
SYSTEM	20V MAX*
TOOL LENGTH	5.3 IN
TORQUE	0-240/ 1,500/1,825 IN-LBS

INCLUDES

- (1) DCF887 - Brushless 1/4" 3-speed Impact driver
- (1) Fast charger
- Kit Box
- (2) DCB203 - 2.0 Ah 20V MAX* XR Batteries
- Belt Clip

WARRANTY & SERVICE INFORMATION

WARRANTY INFORMATION



MANUALS

[INSTRUCTION MANUAL](#) ▶▶

LOOKING FOR SERVICE?

★★★★★ 5.0 | 1 Review

1 out of 1 (100%) reviewers recommend this product



Reviews

[WRITE A REVIEW](#)

Rating Snapshot

Average Customer Ratings