







Search



Rollover image to zoom





DWE5010

1/2" SINGLE SPEED HAMMER DRILL



(0) WRITE A REVIEW

The DWE5010 1/2" Single Speed Hammer Drill has a powerful motor to drive high-speed drilling in dual modes at the user's desired speed. Constructed with a lightweight design and two-finger, rubber trigger for user comfort.

BUY NOW

SHARE THIS PRODUCT:

IMPORTANT LINKS

FEATURES & SPECS

WARRANTY

USER REVIEWS

FEATURES & SPECS

FEATURES

- 7.0 amp motor for increase performance
- Dual mode: hammerdrill/drill for wood, steel or masonry applications
- 3.7 lbs. lightweight design for extended use and less user fatigue
- Two-finger trigger for user comfort
- 360-degree side handle with depth rod offers greater control, versatility, and increased depth accuracy
- Variable speed allows for precise hole placement on work surface
- Compact design (10.3" length) allows for comfortable use and easy access to tight spaces
- · Lock On trigger gives the option to keep the drill running continuously when doing repetitive applications

SPECIFICATIONS

AMPS	7.0 AMPS
BLOWS/MIN	0-47,600 BPM
CAPACITY IN STEEL	1/2 I N
CAPACITY IN WOOD	1-1/4 IN
KIT BOX	NO
POWER TOOL TYPE	CORDED
TOOL LENGTH	10.3 IN
TOOL WEIGHT	3.85 LBS

INCLUDES

- 360° side handle Depth rod
- · Chuck key with holder

WARRANTY & SERVICE INFORMATION

WARRANTY INFORMATION

