



Search



Rollover image to zoom



+ 12

**DWE575**

# 7 1/4" LIGHTWEIGHT CIRCULAR SAW

★★★★☆ 3.0 (2) [WRITE A REVIEW](#)

The DWE575 7-1/4" Lightweight Circular Saw is among the lightest saws in its class at only 8.8 lbs. 15 Amp motor is powerful enough for the toughest applications. Bevel capacity of 57° and 2-9/16" depth of cut capacity provide versatility.

**BUY NOW**

SHARE THIS PRODUCT:

IMPORTANT LINKS

[FEATURES & SPECS](#)

[WARRANTY](#)

[FAQS](#)

[USER REVIEWS](#)

## FEATURES & SPECS

## FEATURES

- One of the lightest saws in its class at 8.8 lbs
- 15 amp motor, powerful enough for even the toughest applications
- 57° beveling capacity with stops at 45° and 22.5°
- 2 9/16 " Depth of cut capacity provides additional versatility of applications
- Anti-s snag Ball bearing lower guard provides smooth guard operation and long life in harsh environments
- Toughcord provides longer durability against cord pull outs
- Integrated dust blower function cleans the line of sight during cutting
- Durable high grade Aluminum smooth base for accurate cuts
- Clear line of sight aids in blade visibility from any angle
- On-board blade wrench storage allows for easy access to the wrench

## SPECIFICATIONS

<b>AMPS</b>	15 AMPS
<b>BEVEL CAPACITY</b>	57 °
<b>BEVEL STOPS</b>	45° / 22.5°
<b>BLADE DIAMETER</b>	7-1/4"
<b>DEPTH OF CUT AT 45°</b>	1.9 IN
<b>DEPTH OF CUT AT 90°</b>	2.55 IN
<b>ELECTRIC BRAKE</b>	NO
<b>MAX WATTS OUT</b>	1,950 W
<b>POWER TOOL TYPE</b>	CORDED
<b>REAR PIVOT</b>	NO
<b>TOOL WEIGHT</b>	8.8 LBS

## INCLUDES

- Carbide tipped 7 1/4" blade
- Blade wrench
- Instruction user manual

## WARRANTY & SERVICE INFORMATION

### WARRANTY INFORMATION