

CT4079-NA

High Voltage
Differential Probe
35 MHz / ± 15 kV

Datasheet

Overview:

Use the CT4079-NA 50-MHz differential probe to make safe and accurate floating measurements with an oscilloscope. The CT4079-NA differential probe allows conventional earth-grounded oscilloscopes to be used for floating signal measurements of up to ± 15 kV for both differential and common mode voltage.



Features:

- 50 MHz bandwidth
- Selectable attenuation settings of 200x or 2000x
- Up to ± 15 kV differential and common mode voltage
- Compatible with most oscilloscopes
- Powered by included 9 VDC mains adapter



Specifications

Operating Parameters	
Bandwidth	50 MHz
Rise Time	7 ns
Attenuation	200x / 2000x
Accuracy	±2%
AC CMRR	-80 dB @ 60 Hz -60 dB @ 100 Hz -50 dB @ 1 MHz
Input Impedance	Between inputs: 40 MΩ // 1.3 pF Each input to ground: 20 MΩ // 2.6 pF
Input Voltage	
Differential Voltage (DC+ACpk)	±1.5 kV / ±15 kV
Common-Mode Voltage (DC+ACpk)	±15 kV or 11 kVrms
Absolute Max Voltage (DC+ACpk)	±15 kV or 11 kVrms
Output Voltage	
Swing	±8 V (±4 V into 50 Ω load)
Source Impedance	50 Ω
General	
Power Supply	External 9 VDC power supply
Power Consumption	200 mA about (9 VDC)
Operating Temperature/ Humidity	0°C to 50°C / 10% to 85% RH
Storage Temperature/Hu- midity	-30°C to 70°C / 10% to 90% RH
Cable Length	100 cm
Input Leads Length	60 cm each
Weight	350 g
Dimensions	220 x 85 x 30 mm