

DIN rail adapter - PTFIX-NS15A-FIX - 3274059

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

DIN rail adapter, with end stop function, width: 10.3 mm, height: 10.8 mm, color: gray, mounting type: NS 15



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	20 STK
GTIN	
GTIN	4055626394145
Weight per Piece (excluding packing)	1.000 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

General

Color	gray
Flammability rating according to UL 94	V0

Dimensions

Width	10.3 mm
Length	28.6 mm
Height	10.8 mm
Height NS 15	13.7 mm

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

DIN rail adapter - PTFIX-NS15A-FIX - 3274059

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27370419
eCl@ss 9.0	27370419

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001024
ETIM 6.0	EC001024

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501