

95 12 165

Cable Shears



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and hard drawn copper conductors
- Precision ground, hardened blades
- Clean and smooth cut without crushing and deformation
- Easy cutting with one-hand operation
- Guard prevents operators' fingers being pinched
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened



Article No.	95 12 165
EAN	4003773029182
Tool	burnished
Handles	with multi-component grips
Style	1
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	15
Cutting capacity copper cable, multiple-stranded mm²	50
AWG	1/0
Length mm	165
Net weight g	250

technical change and errors excepted

