


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **1714001038**
Status: **Active**
Overview: Impel and Impel Plus Backplane Solutions
Description: Impel 92 Ohm, 6 Pair Right-Angle Daughtercard, 1.90mm Pitch, Unguided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.36mm

Documents:

3D Model	Application Specification AS-171320-991-001 (PDF)
Drawing (PDF)	Application Specification AS-171320-992-001 (PDF)
Product Specification PS-171320-999-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-171320-990-001 (PDF)	



General

Product Family	Backplane Connectors
Series	171400
Application	Coplanar, Daughtercard
Application Tooling Documents	TM-622018899
Component Type	PCB Receptacle
Overview	Impel and Impel Plus Backplane Solutions
Product Name	Impel
UPC	887191451046

Physical

Circuits (Loaded)	96
Circuits (maximum)	96
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Nickel, Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	39.256/g
Number of Columns	8
Number of Pairs	6
Number of Rows	12
Orientation	Right Angle
PC Tail Length	1.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Temperature Range - Operating	-55°C to +85°C

Electrical

Current - Maximum per Contact	0.75A
Data Rate	40.0 Gbps
Impedance	92Ω
Shield Type	Full Shield
Voltage - Maximum	150V AC (RMS)

Material Info

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[171400 Series](#)

Mates With

Impel Backplane Header [171395-1807](#) ,
[171395-1808](#) , [172130-1808](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Impel Daughtercard	0622018960
Press-In Tool	

Reference - Drawing Numbers

Application Specification

AS-171320-990-001, AS-171320-991-001,

AS-171320-992-001

Product Specification

PS-171320-999-001

Sales Drawing

SD-171400-0001

Symbol/Footprint Data

SYM-171400-1038

This document was generated on 02/27/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION