

ToLEDo Retro A60

ToLEDo RT A60 CL 806LM E27 SL

0027341



Range Features

-

PRODUCT OVERVIEW

Lamp finish	Clear
Lamp shape	A60
Colour temperature (K)	2700
CRI (Ra)	80
Dimmable	No
EAN code	5410288273419
Energy class	A++
Equivalent watt (W)	60
Cap/Base	E27
Type	ToLEDo Retro A60
Watt (Nominal) (W)	7
Light colour	827 Homelight
Ordering number	0027341
Efficacy (Rated) (lm/w)	115.142857142857
Average life (Rated) (h)	15000
Luminous flux (Rated) (lm)	806
Technology	LED
Voltage (V)	220-240
Colour consistency (SDCM)	6

DATA TABLE

General data

Average life (Nominal) (h)	15000
Control gear required	No
Lamp finish	Clear
Lamp shape	A60
Dimmable	No
Dry applications use only	Yes
EAN code	5410288273419

ToLEDo Retro A60

ToLEDo RT A60 CL 806LM E27 SL

0027341

Energy class	A++
Energy saving lamp	Yes
General application	Hospitality; Residential & Consumer
Intended purpose	No
Cap/Base	E27
Lamp mercury content (mg)	0
Type	ToLEDo Retro A60
No. of switching cycles before premature failure (min)	>50,000
Optimal operating condition (°C)	25
Ordering number	0027341
Product name	ToLEDo RT A60 CL 806LM E27 SL
Average life (Rated) (h)	15000
Special purpose lamp	No
Starting time (max) (s)	0.05
Technology	LED
Transformer required	No
Warm-up time to 60% of full light (max) (s)	< 1s => 60%

Optical data

Colour temperature (K)	2700
CRI (Ra)	80
Light colour	827 Homelight
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	806
Luminous flux (Rated) (lm)	806
Suitable for accent lighting	No
Adjustable chromaticity	No
Colour consistency (SDCM)	6

Electrical data

Drive current (mA)	54
Equivalent watt (W)	60
kWh per 1000 hours burning time	7
Lamp power factor	0.6
Watt (Nominal) (W)	7
Efficacy (Rated) (lm/w)	115.142857142857
Watt (Rated) (W)	7
Voltage (V)	220-240

Physical data

ToLEDo Retro A60

ToLEDo RT A60 CL 806LM E27 SL

0027341

Max. Lamp Diameter (mm) - D	60
Lamp Length (mm) - C/L	104
Lamp dimension equal to filament lamp equivalent	Yes

TECHNICAL DRAWINGS

