



Overview

Model Name	APC Power-Saving Back-UPS Pro 1500, 230V
Includes	CD with software , Qty 1- Detachable IEC Power Cord , Telephone Cable , USB cable , User Manual , Warranty card
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Antigua And Barbuda , Armenia , Australia , Austria , Azerbaijan , Bahrain , Bangladesh , Belarus , Belgium , Benin , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Cayman Islands , Central African Republic , Chad , Chile , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Cote D'Ivoire , Croatia , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , East Timor , Egypt , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guadeloupe , Guinea , French Guiana , Hong Kong , Hungary , Iceland , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , New Zealand , Niger , Nigeria , Norway , Oman , Pakistan , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Tunisia , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , Uruguay , Uzbekistan , Viet Nam , Western Sahara , Yemen , Zambia , Zimbabwe

Output

Output Power Capacity	865 Watts / 1500 VA
Max Configurable Power (Watts)	865 Watts / 1500 VA
Nominal Output Voltage	230V
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Crest Factor	3 : 1
Crest Factor	Line Interactive
Waveform Type	Stepped approximation to a sinewave
Output Connections	(2) IEC Jumpers (Battery Backup) , (5) IEC 320 C13 (Battery Backup) , (5) IEC 320 C13 (Surge Protection)

Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)

Input Connections	IEC-320 C14
Input voltage range for main operations	176 - 294 V
Input voltage adjustable range for mains operation	156 - 300V
Maximum Input Current	0 A
Input Breaker Capacity	10 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	8 hour(s)
Replacement Battery	APCRBC124
RBC Quantity	1

Communications & Management

Interface Port(s)	Optional Simple Signalling RS232 cable , USB
Available SmartSlot™ Interface Quantity	0
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	441 Joules
Filtering	Full time multi-pole noise filtering :10% of IEEE surge let-thgouh : zero clamping response time: instantaneous
Data Line Protection	Analog phone line for phone/fax/modem/DSL (RJ-11 connector) , Network line - 10/100/1000 Base-T Ethernet (RJ-45 connector)

Physical

Maximum Height	301.0 mm
Maximum Width	112.0 mm
Maximum Depth	380.0 mm
Rack Height	0 U
Net Weight	12.7 kg
Shipping Weight	14.3 kg
Shipping Height	387.0 mm
Shipping Width	238.0 mm
Shipping Depth	488.0 mm
Master Carton Units	1.0
Master Carton Weight	0.0 lbs
Color	Black
SCC Codes	1073130426874 8
Units per Pallet	20.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-9000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Audible noise at 1 meter from surface of unit	45.000 dB
---	-----------

Conformance

Approvals	A-tick , C-tick , CE , ENERGY STAR V1.0 (EU) , GOST , GS Mark , TUV , TelePermit
Standard warranty	2 years repair or replace , 3 years repair or replace for European Union countries
Equipment protection policy	Lifetime : 150000 Euros , Lifetime : 200000 AUD , Lifetime : 75000 GBP

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
