



Overview

Model Name	APC Replacement Battery Cartridge #4
Includes	All required connectors , Battery recycling guide , Installation guide , Reusable packaging
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , China , Colombia , Congo , CONGO , THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guatemala , Guinea , Guyana , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Mali , Malta , Mauritania , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

Batteries & Runtime

Battery Volt-Amp-Hour Capacity	0
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	--
Battery mounting	3 - 5
Included Battery Modules	0
Battery Slots Empty	0
RBC Quantity	1

Physical

Net Weight	8.1 lbs (3.68 kg) (3.68 kg)
------------	-----------------------------

Maximum Height	3.9 inches (99.0 mm) (99.0 mm)
Maximum Width	3.7 inches (94.0 mm)
Maximum Depth	5.9 inches (150.0 mm) (150.0 mm)
Shipping Weight	8.81 lbs (4.0 kg) (4.0 kg)
Shipping Width	6.9 inches (175.0 mm) (175.0 mm)
Shipping Height	4.91 inches (124.0 mm) (124.0 mm)
Shipping Depth	8.4 inches (213.0 mm) (213.0 mm)
Rack Height	0 U
Color	Black
Units per Pallet	140.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C) (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters) (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C) (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters) (0-15000 meters)

Conformance

Standard warranty	1 year repair or replace
-------------------	--------------------------