

Performance Specifications

- White High 500 lumen - 4.5 hours - 37 meters
- White Low 130 lumen - 10 hours - 20 meters
- Red High 45 lumen - 8 hours - 13 meters
- Red Low 9 lumen - 19 hours - 7 meters
- Red Flashing 45 lumen - 24 hours

LIGHTING INSTRUCTIONS

- Press 1x to activate work light
 - Press 2x to activate red light
 - Press 3x to activate red hazard flasher
 - Press again to turn OFF
- (Note: Leave any mode On for 8 seconds or longer and your next press of the button turns light Off)*

DIMMABLE BEAM

Each light mode is fully dimmable. Hold button for 1.5 seconds to activate dimming function.

- Light will dim from 100% to 30% over 3 seconds.
- Light will flash quickly when it reaches 30% or 100% to indicate it has reached the lowest or highest light output.
- Release button at any time to achieve desired brightness.
- Light will continue to dim/brighten between 100% and 30% until button is released.

MEMORY POWER SETTING

Big Larry[™]PRO is equipped with memory settings for each light mode. To program memory settings, start in the OFF position.

- Double-tap the button to activate Memory Power Setting. The COB work light will activate.
- Follow Dimming Instructions to adjust light to desired brightness.
- Press button again to move to next setting. Light will cycle through each light mode sequentially.
- Set each light mode at desired brightness level.
- If 100% brightness is desired amongst light modes, simply press button to move to the next mode.
- Press again to turn OFF.

To reprogram, simply repeat the previous steps.

STRAIGHT TO RED INSTRUCTIONS

- Press and hold button for 3 seconds to activate red light.
- Press again to turn OFF.

CHARGING INSTRUCTIONS USING THE MAGDOCK

The MAGDOCK should be connected to a power source using the Micro Charging Cable. Place light on the charging MAGDOCK station. Charging light indicator will remain **RED** until the unit is fully charged, then it will turn **GREEN**.



USING THE MAGCABLE

The MAGCABLE should be connected to a power source using the USB Cable. Place light on the charging MAGCABLE. Charging light indicator will remain **RED** until the unit is fully charged then it will turn **BLUE**.



Recharging may take up to 6 hours based on battery status.

MAGDOCK

(requires included USB to MICRO USB cable)



MAGCABLE



Register for warranty
www.NEBOTools.com