



## TorqueVario STplus Adjustable T-handle



### Details

ASME B107.14m, EN ISO 6789, BS EN 26789  
Tools Marked with Serial No. & Include Calibration Certificate

An economical solution for accurate dedicated Torque Control  
Adjustable 5-14 Newton Meters  
Adjustable with included Setting Tool  
Window Scale Displays Torque Value Numerically  
Ergonomic Handle Design  
Soft Grips for Extrem Comfort  
Get the Highest Torque in a pleasant Way with utterly Control  
Audible and perceptible click when the pre-set torque has been attained  
±6% Accuracy  
Quality & Accuracy Guaranteed to 5000 Cycles or 1 year  
Loosening torque approx. +30% greater than tightening torque

Automatically resets for next torque cycle

### Additional Info

SKU	28940
Weight (lbs)	0.8100
RoHS Compliant	Yes