

Crimping pliers - CRIMPFOX-4,0-ED-6,00 - 1205859

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for CK 4,0... contacts, for 4.0 - 6.0 mm² conductor cross sections

Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 137656
GTIN	4017918137656
Weight per Piece (excluding packing)	686.700 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	256 mm
Width (a)	25 mm
Height	68 mm

General

Color	black
Compression	Square crimp
Designation	Crimping position 1
Max. cross section	4 mm ²
AWG max	12
Designation	Crimping position 2
Max. cross section	6 mm ²
AWG max	10
Weight	560 g
Min. cross section	4 mm ²
Max. cross section	6 mm ²

Crimping pliers - CRIMPFOX-4,0-ED-6,00 - 1205859

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------