

TECHNICAL DATA SHEET



M Type Nylon Cable Gland


**RoHS
Compliant**

| Specification | |
|------------------------|--|
| Description | Material |
| Body | Nylon (PA) |
| Seal and Washer | NBR |
| Properties | V2(UL94), free of halogen, phosphor and cadium |

| M Type Nylon Cable Glands | | | | | | |
|---------------------------|---|----------------|----|----|-----------------|---|
| Part No | Customer Code | Cable Range mm | H | GL | Spanner size mm | Colour |
| M12X1.5 | CB08621/CBBR7371/CBBR7372 | 3-6.5 | 21 | 8 | 15 | Available in Black, Grey, White, Red, Blue |
| M16SX1.5 | | 2-6 | 22 | 8 | 19 | |
| M16X1.5 | CB08622/CB08623/CB08908/CB BR7373/CBBR7374 | 4-8 | 22 | 8 | 19 | |
| M20SX1.5 | | 5-9 | 27 | 7 | 24 | |
| M20MX1.5 | CB08625/CBBR7375/CBBR7376 | 6-12 | 27 | 9 | 24 | |
| M20LX1.5 | | 10-14 | 28 | 9 | 27 | |
| M25X1.5 | CB08627/CBBR7377/CBBR7378 | 13-18 | 31 | 11 | 33 | |
| M32X1.5 | CB08629/CBBR7379/CBBR7380 | 16-21 | 39 | 11 | 42 | |
| M40X1.5 | CB08631 | 22-32 | 48 | 13 | 53 | |
| M50X1.5 | CB08633 | 32-38 | 49 | 13 | 60 | |
| M63X1.5 | | | | | | |

Conditions of use

1. Working temperature -40° to 100°C static state. Instantaneous heat resistance up to 120°C
 -20° to 80°C in dynamic state. Instantaneous heat resistance up to 100°C



Important Notice: This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

