



HD-TVI 2MP Mini-Bullet Camera

CVC637T

3.6mm fixed lens, dark gray housing

CVC637TW

3.6mm fixed lens, white housing



Features

- Full HD resolution over coax
- Additional analog output for 960H
- Compact and lightweight for discreet installations
- Full OSD operation via UTC (up the coax)
- IP66 compliant, weather resistant
- 5 year warranty



Camera Specifications

Image Sensor	1/3" Sony CMOS, 2MP
Resolution	1920 x 1080
Effective Pixels	1984 (H) x 1105 (V)
Total Pixels	2000 (H) x 1121 (V)
Minimum Illumination	0.001 lux
S/N Ratio	More than 50dB
Electronic Shutter	1/30 sec – 1/30,000 sec
Scanning System	Progressive
Synchronization	Internal
Video Output	1.0Vp-p / 75 ohms
TV System	NTSC

Operating Specifications

Power Supply	12VDC (power supply not included)
Power Consumption	200mA
Operation Temperature	14°F - 122°F
Unit Dimensions	1.13" (Dia.) x 2.5" (L)
Unit Weight	4 oz.
Certifications	FCC, RoHS
Signal Distance	up to 1600 ft. (depending on coax quality)

Optional Accessory



PSW5
12VDC
Power Supply

ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 11/15/17