

FLUKE®



Introducing the

## Fluke 279 FC Thermal Multimeter

The industry's **FIRST Thermal Multimeter!**

- Full-featured multimeter with a built-in thermal imager.
- 2-in-1 tool is designed to increase productivity. Do more in less time!
- Rugged and reliable

**For more information, please contact your local Fluke representative.**



## **iFlex® expands your measurement capability!**

### **Specifications**

- Voltage AC/DC: 1000 V
- Current AC: 2500 A AC (with iFlex® flexible current probe)
- Resistance: 50 M  $\Omega$
- Frequency: 100 kHz
- Capacitance: 9,999  $\mu$ F
- Continuity/diode test/min max/display hold
- Resolution: 80 x 60
- Camera Temperature Range: -10 to 200 °C
- 3.5"/8.89 cm color LCD screen
- Certifications CSA, FCC, CE
- CAT III 1000 V, CAT IV 600 V measurement category
- 3 year standard warranty

### **Change the way you see digital multimeters**

**For more information, please contact your local Fluke representative.**