

LED Floodlights



VT-100-W

HIGHLIGHTS :

WATTS



100

EQ. WATTS



LUMINOUS



8000

BEAM ANGLE



100

PRODUCT FEATURES

Item No	: VT-100-W
SKU Code	: 415
Watts	: 100
Voltage	: AC:220-240V,50Hz
Lumen(lm)	: 8000
Color Temperature	: 3000K
Beam Angle	: 100
PF	: >0.9
LED Chip Type	: SMD-Samsung Chip
CRI	: >80
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP65
Body type	: Die casting Aluminium
Dimmable	: -
Life Time	: 30,000 Hours
Operation Temperature	: -25 to +50°C
EAN code	: 3800157629249
Unit size	: 291x240x30mm
Packing details	: 4.00