

LED Panel Series



VT-620RD

HIGHLIGHTS :

WATTS



20

EQ. WATTS



LUMINOUS



2000

BEAM ANGLE



120

Item No	: VT-620RD
SKU Code	: 615
Watts	: 20
Voltage	: AC:220-240V,50Hz
Lumen(lm)	: 2000
Color Temperature	: 4000K
Beam Angle	: 120
Commercial type	: Round
PF	: >0.9
LED Chip Type	: SMD-Samsung Chip
CRI	: >80
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP20
Body type	: ABS+Plastic
Dimmable	: No
Life Time	: 30,000 Hours
EAN code	: 3800157630566
Unit size	: 170x37mm
Packing details	: 40.00

PRODUCT FEATURES

- Contemporary & Elegant Design
- Higher Light Transmission Rate
- No flickering, No U.V Radiation
- No Lead or Mercury content hence Environment friendly
- Suitable for office and general lighting (Conference Room, Showroom, lobby, cabin, kitchen etc.)
- High quality power driver
- Instant light 100% O s
- Temp -20 to + 45°C