



UL/CSA Hook-Up Wire

UL Style1061, CSA AWM I A/B

Product Type:

UL Cable

Application:

These single core cables are mainly used in the internal wiring of electrical and electronic equipment. They are manufactured and approved to UL and CSA specifications

Standards / Conformances:

UL Style 1061

CSA Type AWM I A/B

Vertical flame propagation: complies with CSA FT-1; UL VW-1.

REACH and RoHS Compliant

Construction:

| | |
|-------------|--|
| Conductor: | Tinned annealed copper to UL Subject 758 |
| Insulation: | PVC compound meeting the requirements of: <ul style="list-style-type: none"> Semi-rigid PVC to UL Subject 758 Class 24 to CSA Standard C22.2 No. 210 |

Electrical Characteristics:

Rated Voltage 300V

Rated Temperature -10 °C to 80°C

Physical Characteristics:

| Product Code | Conductor Size (AWG) | Colour | Length m | Nominal Diameter (mm) | Weight (Kg/Km) |
|--------------|----------------------|--------|----------|-----------------------|----------------|
| 6010643 | 26 | Red | 305 | 1.00 | 2.2 |
| 6010096 | 24 | Yellow | 305 | 1.12 | 3.3 |
| 6010696 | 24 | Orange | 305 | 1.12 | 3.3 |
| 6011759 | 24 | Blue | 305 | 1.12 | 3.3 |
| 6012244 | 22 | Yellow | 305 | 1.30 | 4.9 |
| 6010146 | 18 | Brown | 153 | 1.73 | 9.1 |
| 6010148 | 18 | Orange | 153 | 1.73 | 9.1 |