



Sample photo

Order symbol: AR181610SCT
Product nbr: 8561079
Description: PC Enclosure
Remarks: Transparent screw cover

EAN: 6418074066466
El. number:
Finland:

Including: Screw cover base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
Length	Width	Height			
mm:	457	406	ALBP1816 Aluminum Back Panel		
inch:	18.0	16.0	ADFP1816 Dead Front Panel w/ screws		
			ASP1816 Aluminum Swing Panel		
			APSPK1816 Plastic Swing Panel Kit incl. Panel		
			ASPK1816 Swing Panel Kit incl. Panel		
			AMFL16 16" Mounting Flange Set		
Materials:			Rating:		
Material:	Polycarbonate		Ingress Protection (EN 60529): IP66/IP67		
Base colour:	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 0		
Cover screws material:	Stainless steel		UV resistance: UL 508		
Cover colour:	Clear transparent		Flammability Rating: UL 508		
Gasket material:	Polyurethane		Glow Wire Test (IEC 695-2-1) °C: 960		
Temperatures:			NEMA Class:		
Temperature °C (short term):	-40 ... 140 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):					
Temperature °F (continuous):					
Accessories:					
ABP1816	Painted Steel Back Panel				

