



Sample photo

Order symbol: AR884SCT
Product nbr: 8561091
Description: PC Enclosure
Remarks: Transparent screw cover

EAN: 6418074066329
El. number:
Finland:

Including: Screw cover base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
Length	Width	Height	ABP88	Painted Steel Back Panel	
mm:	203	203	102	ALBP88	Aluminum Back Panel
inch:	8.0	8.0	4.0	ADFP88	Dead Front Panel w/ screws
Materials:			ASP88	Aluminum Swing Panel	
Material:	Polycarbonate		ASPK88	Swing Panel Kit incl. Panel	
Base colour:	RAL 7035 -light grey		ASPHK8	Swing Panel Kit w/o Panel	
Cover screws material:	Stainless steel		AMFL8	8" Mounting Flange Set	
Cover colour:	Clear transparent		Rating:		
Gasket material:	Polyurethane		Ingress Protection (EN 60529): IP66/IP67		
Temperatures:			Electrical insulation: Totally insulated		
Temperature °C (short term):	-40 ... 140 °C		Halogen free (DIN/VDE 0472, Part 815): 0		
Temperature °C (continuous):	-40 ... 80 °C		UV resistance: UL 508		
Temperature °F (short term):	-40 ... 284 °F		Flammability Rating: UL 508		
Temperature °F (continuous):	-40 ... 175 °F		Glow Wire Test (IEC 695-2-1) °C: 960		
Accessories:			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13		
APBP88	PVC Back Panel				

