



Order symbol: AR12105FSC
Product nbr: 8561689
Description: PC Enclosure
Remarks: Opaque flat screw cover

EAN: 6418074098627
EI. number:
Finland:

Including: Flat screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting

Sample photo

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	305	254	127	ALBP1210	Aluminum Back Panel
inch:	12.0	10.0	5.0	ADFP1210	Dead Front Panel w/ screws
Materials:				ASP1210	Aluminum Swing Panel
Material:	Polycarbonate			ASPK1210	Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey			ASPHK12	Swing Panel Kit w/o Panel
Cover screws material:	Stainless steel			AMFL10	10" Mounting Flange Set
Cover colour:	RAL 7035 -light grey			Rating:	
Gasket material:	Polyurethane			Ingress Protection (EN 60529): IP66/IP67	
Temperatures:				Impact Resistance (EN 62262): IK07/IK08	
Temperature °C (short term):	-40 ... 140 °C			Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (short term):	-40 ... 284 °F			UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F			Flammability Rating: UL 508	
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960	
ABP1210	Painted Steel Back Panel			NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
				Certificates:	
				Gost R	

