




Main

Range	ClimaSys
Product name	ClimaSys CA
Product specific application	Outdoor heavy duty
Range compatibility	Spacial SFHD Spacial S3HD Thalassa PHD ClimaSys CV fan
Product certifications	UL conforming to UL 94 CE conforming to ENV 1630
Product or component-type	Outlet grille
Accessory / separate part category	Thermal management accessory
Accessory / separate part destination	ClimaSys ventilation system
Mounting location	Sides of enclosure
Mounting position	Vertical
Fixing mode	By screws
Device composition	4 x screw 1 x G3 M1 synthetic standard filter 1 x support frame 1 x external part

Complementary

Material	Polyamide 6 Stainless steel Steel
Colour	Grey (RAL 7035) external part Green (Pantone 355C) internal part
Surface finish	Epoxy-polyester powder
Cut-out dimensions	223 x 223 mm
Height	External : 315 mm
Width	External : 300 mm
Depth	External : 60 mm
IP degree of protection	IP55 (outdoor)

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
RECh	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.