## Product data sheet Characteristics

### NSYCR100WU2

## ClimaSys PTC heating resistance 100W 110-250V



# Main Range ClimaSys Product name ClimaSys CR Product or component-type Range compatibility Prisma P Prisma G Power range 90 W Input voltage 110...250 V AC 50/60 Hz

### Complementary

Operating position	Vertical	
Ambient air temperature for operation	-4070 °C	
IP degree of protection	IP20	
Product certifications	VDE UL	
Material	Extruded aluminium for body	
Height	200 mm	
Width	85 mm	
Depth	65 mm	
Condition of use	Heaters must be installed with a thermal controller Electrical protection is needed Air sealed enclosure	
Fixing mode	By clips	
Mounting support	35 mm DIN rail	

#### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold

### Contractual warranty

Marranticanian	10 months
Warranty period	10 MONUIS

nmercialised