



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component-type	Resistance heater with fan and thermostat
Power range	400...550 W
Input voltage	230 V AC 50/60 Hz
Electrical connection	2 screw terminals 2.5 mm ²

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
Temperature setting range	0...60 °C
IP degree of protection	IP20
Product certifications	UL VDE
Height	150 mm
Width	155 mm
Depth	215 mm
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**