Product data sheet Characteristics

NSYCVF170M230

Climasys forced vent. 170 m3/h, 230V without grille



Main Range ClimaSys Product name ClimaSys CV Product or component-type Range compatibility Prisma P Air flow Free flow rate: 170 m3/h at 50 Hz Input voltage 230 V 50/60 Hz

Complementary

Power range	17 W	
Noise level	41 dB	
Height	External: 119 mm	
Width	External: 119 mm	
Depth	External: 38 mm	
Product weight	0.82 kg	
Material	Steel for protective grille	
Device composition	axial motor protective grille on the front and rear surfaces fixing collar	

Offer Sustainability

	Reference not containing SVHC above the threshold	
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity	

Contractual warranty

Warranty period	18 months

D 1 11:6 01 1	A 1 1 1 1
Product Life Status:	Commercialised
T TOUGHT HE STAIRS	COMMERCIANSEC