



## **CT3888: Fully Insulated BNC female to 4 mm Banana Plugs, General Purpose**

### **DESCRIPTION:**

Insulated BNC female to 4 mm banana plugs coax adapter. Adapts a BNC male cable, component or equipment to double banana plugs.

Fits standard or shrouded (sheathed) pair banana jacks on standard 19 mm (.75") centers. Used for interconnection to power supplies, function generators and other test instrumentation. A very versatile adapter.

### **Features:**

- Fully insulated, plastic, BNC female
- 19 mm (.75") plug spacing
- RoHS 2 compliant



**SPECIFICATIONS:**

IEC Rating	<30 Vac / <60 Vdc
Current	3 A
Impedance	50 $\Omega$
Temperature	0° to +50° C
RoHS (2011/65/EU)	Compliant