## Product data sheet Characteristics

## **GV2G445**

Linergy FT - Comb busbar - 63 A - 4 tap-offs - 45 mm pitch



Range of product	TeSys GV2	
	TeSys fuse-disconnector	5
	TeSys D	g
	TeSys U	<u>-</u>
	TeSys K	i
Range	Linergy	for s
Product name	FT	_ stole
Device short name	GV2G	_ ong e
Product or component type	Comb busbar	-thes
Accessory / separate part category	Connection accessory	
Poles description	3P	eliability
Range compatibility	TeSys - GV2	
	TeSys - U	suitability
	TeSys - D	7
	TeSys - K	S
Number of tap-offs	4	—iii
[Ith] conventional free air thermal	63 A	_detel
current		for
Connection pitch	45 mm	— Pesi-
		— a

## Complementary

Mounting location	On terminal	
[Ui] rated insulation voltage	690 V	
Length	180 mm	
Product weight	0.077 kg	
Compatibility code	GV2G	

## Contractual warranty

Warranty period	18 months		