

pro-ELEC

A Unique Blend of Style and Technology

PRO-ELEC

400lm LED Candle Lamp

Model	PE-LC011713
Lumen	400lm
Watt	5W
Voltage	220V-240V
Lifetime	30000h
On/off	≥15000
Colour temp	4000K
Ra	≥80
Quick ign	<1s = 100%
Hg	0.0mg
Use in dry locations only	

Made in China PQ2 SPP

Cool White B22/BC

CE

Not applicable

Lamp Style	: Candle
Lamp Base Type	: B22
LED Colour	: Cool White
Dimmable	: No
Luminous Flux	: 400lm
Power Rating	: 5W
Voltage Rating	: 220-240V AC, 50Hz
Life Span	: 25000h
On/Off	: 15000x
Temperature	: 4000K
CRI	: 80
Beam Angle	: 250° (Deg.)
Equivalent Power	: 35W
Efficiency Rating	: A+
Power/1000h	: 5kWh/1000h
Dimensions (L × D)	: 102mm × 38mm

Description	Part Number
LED Lamp, Candle, B22, Cool White, 5W, 38mm, 4 Pack	PEL00176

www.farnell.com
www.cpc.co.uk

pro-ELEC