

2.5" SATA/SAS HDD/SSD mobile rack for slim ODD or slim FDD bay



Support 7~9.5mm drive height



Un-screw 3 screws to remove the metal ODD bracket



EAGLE HOOK

FULL METAL CONSTRUCTION



HDD POWER HDD ACTIVITY NO HDD (APT)

Supports 7pin SATA Locking Latches



## ToughArmor MB411SPO-B Features & Specs

- Ideal 2.5" mobile rack for system that has tight space constraints such as embedded systems, mobile computers, rackmount computers, rackmount systems, industrial automation control system, military computers and OEM / ODM systems
- Ultra small form factor design for maximum space saving
- Fits 1 x 7mm to 9.5 mm height 2.5" SAS/SATA HDD /SSD in a slim ODD or slim FDD bay
- Supports 2.5" SAS (single channel)/SATA HDD/SSD up to 6Gbps transfer rate (SAS host is required for SAS drives)
- Removable EZ Slide Micro drive tray for easy maintenance
- Heavy duty full metal construction designed for perfect for enterprise applications
- Multi-Flow Technology provides excellent passive cooling
- Anti-Vibration Technology creates a safe environment for hard drives or SSDs
- Active Power Technology (APT) powers up individual LED if only there is drive installed in the drive bay
- EMI Grounding protects hard drives from electrical damage
- Locking latch designed for SATA 7 pin data port

Model Number	MB411SPO-B
Color	Black
Host Interface	Single 7pin SATA (Support SAS single channel)
Drive Fit	Single 2.5" SAS/SATA HDD/SSD (SAS host required for SAS drives)
Compatible 2.5" Drive Heights	7mm, 9.5mm
Device Fit	Slim ODD or Slim FDD bay
Transfer Rate	Up to 6 Gb/sec. (depending on hard drive speed)
Power Input	Mini 4-pin power wafer
Insert & Extract connection Via	Direct SAS/ SATA hard drive connection
Structure	Full metal
Drive Cooling	Metal heat dispersion
Power Indicator	Solid green LED
HDD Access Indicator	Flashing green LED
Dimension (L x W x H)	127.0 x 25.6 x 130mm
Weight	403g
Package Contents	Device, user manual and screws