



Product Specification



IND3LS5DS

Indulux LED D/S M3 ST



ABB Emergi-Lite

United Kingdom
Sales +44 (0) 333 999 9900
Email: LV.Enquiries@gb.abb.com
www.emergi-lite.co.uk

United Arab Emirates
Tel: +971 (4) 3147500
E-mail: info@ae.abb.com

Product Information

Catalogue Number	IND3LS5DS
Category	Combined Escape route or Sign Luminaire
GID	7TCA091720R0179
GTIN	05415022466904
Family	Indulux
Warranty (Year)	3
Other	0

Characteristics

Power Supply System	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Ceiling; Wall
Mounting form	Surface
Material housing	316L stainless steel/plastic
Colour housing	White/Grey
Material cover	No cover supplied
Material	316L stainless steel/plastic
Colour	Silver/Clear
Length (mm)	398
Width (mm)	100
Height/depth (mm)	100
Maximum outer diameter (mm)	108
Built-in length (mm)	surface N/A
Built-in width (mm)	surface N/A
Built-in diameter (mm)	surface N/A
Built-in depth (mm)	surface N/A
Nominal Voltage (V)	220-240
Voltage type	AC 50Hz
Duration (Hours)	3
Battery	NiMh
Monitoring equipment	0
With lamp	Yes
Lamp Type	LED
Lamp holder	Other
Lamp Power (w)	10
Number of lamps	2
Light output in emergency operation (lm)	400
Average lifespan light source (hours)	60000
Colour of light	white
Colour Temperature (K)	6000K
CRI	80
Protection class	II
Degree of Protection (IP)	68
With remote switch connection	Yes
Wiring system	Maintained / non-maintained circuit
Type of Legend	Varies
Material type	Internal Foil supplied
Recognition distance (m)	17



Circuit	0
Impact strength (IK)	10
Apparent Power Consumption maintained mode (VA)	7 15
Nominal current (mA)	65
Inrush Current (A-0.1ms)	0
Powerfactor	0.48
Temperature range (0'C)	0-40

Article Details

Product class	Emergency luminaire
E-code	0
Discount group	0
Harmonized code	
GLN	0

Ordering Information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (Kg)	2
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	430 x 130 x 140