

TECH SPECS

DISPLAY

14" full HD LCD screen	1920 x 1080 resolution
180° screen angle range	

RASPBERRY PI 3

1.4GHz quad-core arm cortex A53P	4 USB ports
40 GPIO pins	HDMI port
Gigabit Ethernet port	802.11 B/G/N dual-band wireless LAN
Bluetooth 4.2	3.5mm audio jack
Camera interface	Display interface
Micro SD card slot	Videocore IV 3D graphics core

CHASSIS

6-8 hour battery life	105mm sliding keyboard for internal access (US layout)
104x75mm trackpad with Gesture Control	Modular Rail for pi-top accessories

INCLUDED HARDWARE

18V, 2.5A charger with AU, EU, UK and US adapters	8GB class 10 SD CARD with pi-topOS
SD Card Removal Tool	

FURTHER INFO

Please note: not compatible with pi-topSPEAKER mk1	Version can be identified on underside of the pi-topSPEAKER
--	---