



SP-7/4SQS

Order No.: 10.3590

Price upon request

PRODUCTINFOS

Universal speaker, 4 W, 4 Ω

- Magnetic shielding
- For standard applications
- Sound pressure from approx. 200 Hz on

TECHNICAL SPECIFICATIONS

SP-7/4SQS

Impedance (Z)	8 Ω
Frequency range	f3-17000 Hz
Power rating	4 W
Peak music power output	8 W
Magnet diameter	Ø 43.5 mm
Mounting cutout	Ø 61 mm

SP-7/4SQS

Mounting depth	32.7 mm
Mounting hole diameter	Ø 73.5 mm
Dimensions	66.5 x 33.5 mm
Width	66.5 mm
Height	66.5 mm
Depth	33.5 mm
Admiss. ambient temp.	0-40 °C
Weight	139 g
Sales unit	1