



SP-167E

Order No.: 10.3970

PRODUCTINFOS

Hi-fi bass-midrange speaker, 35 W, 4 Ω

- Great all-round speaker
- Foam surround
- Replacement speaker for closed speaker systems and bass-reflex speaker systems

TECHNICAL SPECIFICATIONS

SP-167E

Impedance (Z)	4 Ω
Frequency range	f3-6,000 Hz
Resonant frequency (fs)	62 Hz
Power rating	35 W
Peak music power output	70 W
Sensitivity	92 dB/W/m

SP-167E

Suspension compl. (Cms)	0.7 mm/N
Moving mass (Mms)	9.3 g
Mech. Q factor (Qms)	2.78
Electr. Q factor (Qes)	0.48
Total Q factor (Qts)	0.41
Equivalent volume (Vas)	17.88 l
DC resistance (Re)	3.9 Ω
Force factor (BxL)	5.43 Tm
Voice coil induct. (Le)	0.6 mH
Voice coil diameter	Ø 25.5 mm
Voice coil former	aluminium
Linear excursion (X _{MAX})	± 2.5 mm
Eff. cone area (Sd)	135 cm ²
Magnet weight	570 g
Magnet diameter	Ø 100 mm
Mounting cutout	Ø 149mm
Mounting depth	67 mm
Mounting hole diameter	Ø 160 mm
Dimensions	Ø 169 mm x 70 mm
Outside diameter	Ø 169 mm
Width	Ø 169 mm
Depth	70 mm
Admiss. ambient temp.	0-40 °C
Weight	1.23 kg
Sales unit	1
Type of speaker	6.5