



Sample photo

Order symbol: PC H 95 G
Product nbr: 8724315
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074002273
El. number:
Finland: 3423417
Electric No. Denmark: 8212001653
Electric No. Italy: 7201050
Electric No. Sweden: 2536826

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
mm:	170	140	95	CHM-3	DIN-35 Mounting rail
inch:	6.7	5.5	3.7	DH-3	DIN-35 Mounting rail
				FP 22046	Wall fastening lug (4 pcs)
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK08	
Cover screws material:	Polyamide			Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey			UV resistance: UL 508	
Gasket material:	Polyurethane			Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 4X, 6, 12, 13	
Temperatures:				Certificates:	
Temperature °C (short term):	-40 ... 120 °C			Germanischer Lloyd (GL)	
Temperature °C (continuous):	-40 ... 80 °C			SGS Fimko	
Temperature °F (short term):	-40 ... 250 °F			Gost R	
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
H-MP	Mounting plate				

PICCOLO 170x140x95

