

PICCOLO PC M 95 T



Sample photo

Order symbol:	PC M 95 T
Product nbr:	8724018
Description:	Enclosure, PC
Remarks:	Transparent cover

EAN:	6418074002303
El. number:	
Finland:	3423519
Electric No.	8212001776
Denmark:	
Electric No. Italy:	7202060
Electric No. Sweden:	2536859

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	230	140	95
inch:	9.1	5.5	3.7

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	Clear transparent
Cover screws colour:	Grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:

M-MP	Mounting plate
------	----------------

Accessories:

CHM-3	DIN-35 Mounting rail
FM-3	DIN-35 Mounting rail
FP 22046	Wall fastening lug (4 pcs)

Rating:

Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4X, 6, 12, 13

Certificates:

Germanischer Lloyd (GL)
SGS Fimko
Gost R

PICCOLO 230x140x95-125

