



Model No. 703EURD

89mm long zinc plated hard wrought steel hasp with hardened steel locking eye

Best Used For:



Cabinets



Residential Gates & Fences



Sheds, Workshops & Garages



Tool Chests & Tool Boxes

Security Level:



Basic to medium security:

Generally recommended for indoor general purpose

Overview & Features

Product Features

- 89mm hard wrought steel body
- Accepts shackle diameter up to 9mm
- Zinc plated hardened steel for added strength and weatherability
- Hardened steel staple resist cutting and sawing
- Hardened steel locking eye for strong cut resistance
- Tamper proof hinge for pry resistance
- Mounting hardware included for easy installation

Product Details

The Master Lock No. 703EURD Hasp features a 89mm long hard wrought steel body. The zinc plated hardened steel hasp provides added strength and weatherability. The hardened steel staple and locking eye resist cutting and sawing. The ribbed hasp plate offers extra strength, and hardened steel locking eye provides strong cut resistance. The Limited Lifetime Warranty provides peace of mind from a brand you can trust.

Product Specifications

Product Number	703EURD
Lockout Hasp Length	89mm
Accepts Shackle Diameter up to	9mm
Description	Retail Carded Packaging
Shelf Pack Qty	4
Master Carton Qty	24

Master Lock Europe S.A.S.

10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O: +33-1-41437200 | F: +33-1-41437204
www.masterlock.eu