

Product information

230MM ANGLE GRINDER



GA9020KD

Bore Diameter	22 mm
Noise sound pressure	89 dB(A)
Noise sound power	100 dB(A)
Noise K factor	3 dB(A)
Spindle Size	M14x2mm
Max Wheel Diameter	230 mm
Input wattage	2000 w
No Load Speed	6600 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Artificial Wheel	5.5 m/sec ²
Net weight	5.76 - 8.05 kg



STANDARD EQUIPMENT: Lock nut wrench, Side handle, Diamond wheel, Carry case

- Large trigger switch.
- Double Insulation
- Machined bevel gears.
- Gear housing can be positioned at every 90 degrees.

Details correct as of: 6-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com