



DEWALT XR FLEXVOLT Reciprocating Blade 8 Piece Set 152-230mm 4/6TPI - 14/18TPI

DT99551-QZ



- Increased efficiency for maximum cordless run time
- Up to 2 X longer life compared to standard blades
- Improved longer run time
- Variable tooth designs provide increased blade efficiency and a reduction of tooth breakage
- Tough Coat reduces friction and heat build up
- Ideal for wood and metal applications

Description:

The DEWALT XR FLEXVOLT Reciprocating Blade 8 Piece Set 152-230mm 4/6TPI - 14/18TPI, has been designed for increased efficiency and maximum run time. The blade can last up to 2x longer compared to a standard construction blade. With variable tooth designs the blades have increased efficiency which reduces tooth breakage. The bi-metal blades are coated with a special Tough Coat finish which reduces friction and heat buildup for longer life. Ideal for cutting woods, particle boards, metals, piping, plastics, pvc and more. The blades have been optimised to fit XR FLEXVOLT power tools for high demanding jobsite operations.

Specifications	
Kit Contains	8 Pieces
Application	Metal, Plastic, PVC, Wood
Cutting Length	152, 203, 230 mm
Number of Teeth per Inch	4/6, 14/18 TPI
Blade material	Steel

Supplied With:

- 3 x 152mm (6") 4/6 TPI Saw Blades
- 1 x 230mm (9") 4/6 TPI Saw Blades
- 3 x 152mm (6") 14/18 TPI Saw Blades
- 1 x 203mm (8") 14/18 TPI Saw Blades
- 1 x Blade Carry Case