

S138



Socket sets 1/4", 3/8" and 1/2"

- 1/4" and 1/2" sockets, and combination spanners set
- High performance alloy steel
- Matt finish
- ISO 1174
- DIN 3120
- Case: High Density Polythene (HDPE)
- Contents, 138 pcs
 - 12 pcs 1/4" hexagon sockets: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm
 - 10 pcs 1/4" hexagon deep sockets: 4, 5, 6, 7, 8, 9, 10, 11, 12, 13 mm
 - 1 pc 1/4" reversible ratchet 60 teeth and two component handle, L = 150 mm
 - 1 pc 1/4" spinner handle: 2-component handle, L = 150 mm
 - 1 pc 1/4" sliding T-bar: L = 106 mm
 - 1 pc 1/4" extension bar: 50 mm
 - 1 pc 1/4" extension bar: 100 mm
 - 1 pc 1/4" universal joint
 - 1 pc 1/4" bit holder
 - 1 pc 1/4" flexible extension bar: 150 mm
 - 16 pcs 3/8" hexagon sockets: 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22 mm
 - 1 pc 3/8" reversible ratchet 60 teeth and two component handle, L = 200 mm
 - 1 pc 3/8" spark plug socket: 21 mm / 13/16"
 - 1 pc 3/8" spark plug socket: 18 mm
 - 1 pc 3/8" spark plug socket: 16 mm / 5/8"
 - 1 pc 3/8" universal joint
 - 1 pc 3/8" extension bar: 75 mm
 - 1 pc 3/8" extension bar: 150 mm
 - 18 pcs 1/2" hexagon sockets: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 32, 34 mm
 - 9 pc 1/2" hexagon sockets: 3/8", 7/16", 1/2", 9/16", 11/16", 3/4", 13/16", 7/8", 1.3/16"
 - 1 pc 1/2" reversible ratchet 60 teeth and two component handle, L = 250 mm
 - 1 pc 1/2" sliding T-bar with double function, 1/2" head 3/8F-1/2"M adapter
 - 1 pc 1/2" extension bar: 125 mm
 - 1 pc 1/2" extension bar: 250 mm
 - 1 pc 1/2" Universal joint
 - 1 pc bits adapter: 1/4" square drive
 - 4 pcs Pozidriv bits: PZ 0, 1, 2, 3
 - 5 pcs Phillips bits: PH 0, 1, 2, 3, 4
 - 3 pcs Flat bits: 4, 5.5, 7 mm
 - 6 pcs Insert bits: 3, 4, 5, 6, 8, 10 mm
 - 9 pcs Torx bits: T 8, 10, 15, 20, 25, 27, 30, 40, 45
 - 1 pc Bits ratchet
 - 3 pcs Hexagon keys: 1.5, 2, 2.5 mm
 - 8 pcs Crow foot wrenches: 10, 11, 13, 14, 15, 17, 18, 19 mm
 - 13 pcs Combination spanners: 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19 mm



S138



7314150195022



2



10580