





## Laser Measuring Tool

Item No.: 2270075

Ident No.: 11016

Bar Code: 4006825616187

The Einhell laser distance meter TC-LD 25 is a small and handy pocket-sized tool for performing easy and precise measurements of distances up to 25 meters. This meter lets you measure distances in next to no time and also calculate areas and volumes. The interface for measuring has variable settings to allow measuring from either the front or rear edge. The min/max function allows continuous measurements. Thanks to its soft grip, the laser distance meter is comfortable to handle. For safety there is a safety function: the laser beam is only activated after the switching on operation is repeated. It switches off automatically after three minutes without being used. Supplied in a practical bag.

## **Features**

- Easy and precise measurement of distances up to 25 m
- Measurements from the front or back edge of the device
- Easy measurement of lengths, areas or volumes
- Min/max function for continous measurements
- Safety function: laser radiation only with repeated power-up
- Small and convenient to use laser measuring device in pocket size
- Comfortable handling thanks to the soft grip
- Automatic switch-off after 3 minutes of inactivity
- Incl. practical bag for storage
- 2x 1,5V AAA batteries needed (not included in delivery)

## Technical Data

- Working range 0.05 m - 25 m +/- 3 mm/m - Measurement accuracy - Laser type class - Laser diode 635 nm - Automatic deactivation 3 min

## **Logistic Data**

0.09 - Product weight (kg) - Gross weight (kg) 0.28

113 x 400 x 270 mm - Dimensions single packaging

10 Pieces - Pieces per export carton - Gross weight of export carton 2.8 kg

- Dimensions export carton 365 x 245 x 220 mm - Container quantity (20"/40"/40"HC) 13800 | 28200 | 33840













