

Magnetic Buzzer-

41.S78P050A-LF

IMO

■ MT Buzzer Single 5VDC Pin Noryl

■ Colour - Black

General Specification

Model Number	41.S78P050A-LF
Operating Voltage Range (VDC)	4.0~ 7.0
Rated Voltage (VDC)	5
Max. Rated Current* (mA)	30
Min. Sound Output* (dBA / 10cm)	85
Frequency* (Hz)	2300 +/- 300
Tone Nature	Single
Operating Temperature (°C)	-40~ +85
Terminal	Pin
Housing Material	Noryl
Weight (g)	2

* Value applying rated voltage



Dimension (mm)

