



PDM-302

Order No.: 23.5560

Price upon request

PRODUCTINFOS

PA desktop microphone,

with gooseneck.

- Dynamic, cardioid polar pattern
- Low-noise push-to-talk switch, latching or non-latching
- 5 m connection cable with XLR plug, balanced

TECHNICAL SPECIFICATIONS

PDM-302

Type	desktop microphone
Transmission method	cable
Polar pattern	cardioid
System	dynamic

PDM-302

Audio frequency range	60-12,000 Hz
Nominal impedance	600 Ω
Sensitivity	3.2 mV/Pa
Gooseneck length	310 mm
Admiss. ambient temp.	0-40 °C
Dimensions	120 x 60 x 160 mm (console housing)
Weight	1 kg
Cable	5 m
Connection	XLR, bal.