



Description:

Cost effective 6" ceiling loudspeaker offering full range audio delivered utilising a dual cone driver, the loudspeaker is ideally suited for general background music and speech reinforcement. The loudspeaker is simple to install using the spring clips and a template is supplied for convenience.

Features:

- Dual cone driver for extended upper frequency response
- Multiple power taps
- Low profile design blends into environments
- ABS baffle with metal grille
- Spring clip mounting for easy installation
- Supplied with template to aid installation

Specifications:

Power taps @ 100V: 3W, 6W, 9W

Power taps @ 70V: 1.5W, 3W, 4.5W

Impedance: 1.1 K Ω , 1.7K Ω , 3.3K Ω

Sensitivity (1W/1m): 91dB (\pm 3dB)

Maximum SPL (Rated W/1m): 101dB

Frequency response: 80Hz-18kHz

Drivers: 6" full range dual cone

Connections: Flying leads

Cutout: 170mm \varnothing

Dimensions: 80 x 200mm \varnothing

Weight: 0.9kg