



OD Series Water Resistant Speakers – OD6-W4/W8



A range of water resistant speakers for panel mounting, suitable for PA installations in swimming pools, bathrooms etc.

- 2-way speakers
- 5cm (2") tweeter with mylar cone
- IP35 rated
- Plastic enclosure
- Spade terminal connections (6mm)
- Woofer with polypropylene cone
- Built-in crossover
- Includes fixing kit
- Gasket included
- Supplied in pairs

	125.061UK	125.063UK
Colour	White	White
Impedance	4 ohms	8 ohms
Speaker size	165mm (6.5")	165mm (6.5")
Frequency response	80Hz - 20kHz	80Hz - 20kHz
Power max.	100W	100W
Power rms	40W	40W
Magnet weight	221g (7.8 oz)	221g (7.8 oz)
Cutout	132mmØ	132mmØ
Mounting depth	65mm	65mm
SPL @ 1W/1m	87dB	87dB
Dimensions	84.5 x 180mmØ	84.5 x 180mmØ
Weight	745g	745g
Humidity max.	95%	95%
Dispersion angle	140°	140°
Temperature range	-20 - 85°C	-20 - 85°C

